

# CLEANING the manifold body

Degreasing before welding

Case study for :




A French company specialising in the design and manufacture of pumps and pumping systems called on MecanoLav to wash its manifold casings.

**MecanoLav**  
Smart Cleaning



- Internal and external cleaning of parts up to 3 metres long
- Achieve appropriate cleanliness prior to welding operation
- Perfect drying



Appropriate cleaning

- Machine with inclined horizontal chamber for parts up to 3 metres long
- Crimping system for cleaning parts of different lengths and diameters [ from 500 to 3000 mm in length] and [ from 42 to 273 mm in diameter].
- Interchangeable fixtures specifically adapted to multiple part references by length and diameter



Targeted action

- Internal and external cleaning of each part number
- Targeted spraying for internal cleaning of each part size
- Double bath: 1 washing bath and 1 rinsing bath for a high standard of cleanliness before welding operations